



Pass and Seymour  
Manual Controllers  
Part No. 7862R



Manual Control Switch 2-Pole 60A 600V in NEMA 3R Enclosure. Slotted opening on enclosures allows for lock-out, tag-out functionality.

## Features & Benefits

- High horsepower rating, up to 3HP for heavy-duty applications
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).
- Compact design provides ease of installation
- Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life
- Made in USA
- Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements
- Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom
- Accepts #4 AWG
- cULus listed

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007078619
Country Of Origin	United States	Standard	UL Listed
Type	Manual Controller		

### Dimensions

Product Width US	1.74 in	Product Depth US	1.66 in
Product Height US	3.75 in		

---

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

---

Technical Information

Amperage	30 A	Wire Size	#14 - #10 AWG
----------	------	-----------	---------------

Voltage	600.0 V		
---------	---------	--	--

---