



Manual Control Switch 3-Pole 60A 600V in NEMA 3R Enclosure. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Standard	UL Listed

Dimensions

Product Width US	1.74 in	Product Depth US	1.66 in
Product Height US	3.26 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

---

Amperage	30 A	Voltage	600.0 V
----------	------	---------	---------

---