Ortronics
66M150 Block With 89D Bracket
Part No. 8050M66M150

Ortronics pre-wired 66 blocks can be used to provide network interface connections between voice and data equipment and the public telco network as well as modular wiring connections for key telephone systems.

Features & Benefits

Can be used to provide network interface connections between voice and data equipment

Supports modular wiring connections for key telephone systems

10 in. x 2.84 in. x 2.71 in.

Specifications

General Info

Product Line	Ortronics	Color	Ivory
UPC Number	662875154730	Country Of Origin	Mexico
Product Type	Punchdown Block	Application Sector	Commercial, Industrial
Standard	UL Standard	Warranty Type	5-Year

Dimensions

Product Width US	10.0 in	Product Depth US	4.0 in
Product Height US	1.0 in		

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat3
Compatibility	25 Pair Telco	Storage Humidity	0-100% RH
Plating Specification	Gold	Operating Temperature Max	60 °C
Amperage	1.5 A	Connector Type	110

Wattage	100 W	Operating Humidity	0-90% RH (Non-Condensing)
Voltage	60.0 V	Storage Temperature	-40° - 60° C