



Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 20A 125V

Features & Benefits

Impact-resistant nylon face.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Auto-ground clip assures positive ground.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------
