



Wiremold
861QTC Series Wood Floor Box Assembly
Part No. 861QTCGY



Complete with prewired 15A quad receptacle can be wired as standard or isolated ground. Flush poke-thru-style flanges available in a variety of colors/finishes. Slide covers match painted flange colors. Aluminum and brass covers shipped with black slide covers. Brass flange also available with nonmetallic brass-color slide holder. Die-cast aluminum construction with three 1/2" trade size knockouts: two on the sides and one on the bottom. 18 cu. in. (295 cu.cm) capacity. Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

Features & Benefits

| | |
|---|---|
| Complete with prewired 15A quad receptacle can be wired as standard or isolated ground. | Flush poke-thru-style flanges available in a variety of colors/finishes |
| Slide covers match painted flange colors | Aluminum and brass covers shipped with black slide covers |
| Brass flange also available with nonmetallic brass-color slide holder | Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors. |
| Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors. | |

Specifications

General Info

| | | | |
|---------------------|--|-------------------|---|
| Product Line | Wiremold | Finish | Painted |
| UPC Number | 786564013273 | Country Of Origin | Mexico |
| Construction | Assembled | Cover Style | Flush |
| Number of Knockouts | 3 | Cover Material | Die-Cast Aluminum |
| Application Sector | Commercial | Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. |
| Warranty Type | 1-Year from Installation or 2-Years from Day of Sale | Type | Floor Box |

Dimensions

| | | | |
|-------------------|--------|----------------|--------------------|
| Product Weight US | 2.5 lb | Cubic Capacity | 18 in ³ |
| Knockout Size | 1/2 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|---------------------|--------------|------------------|----------|
| Floor Type | Raised, Wood | Service Capacity | Single |
| Minimum Floor Depth | 1 in | Amperage | 15 A |
| Box Capacity | 1 Gang | Cable Entry | knockout |
| Number of Outlets | 4 | | |