




Wiremold
Omnibox® Series Triple Gang Shallow Steel Floor Box
Part No. 880M3



The 880M3 shallow three gang Omnibox® Floor Box provides an excellent activation solution for applications where multiple services are required in open space areas. The 880M3 floor box is offered in a stamped steel construction, designed to be installed in above grade concrete floor applications and to meet a wide range of market requirements.

This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.

Features & Benefits

TopGuard protection. All cover assemblies for the Omnibox Floor Box Series have TopGuard protection. An integral design which keeps out water, dirt, and debris from the power and communication compartments.

Watertight cast-iron construction. Meets requirements for on grade or below grade application Three-gang configurations, maximum flexibility. Can remove divider for greater capacity. Supports multiservice applications.

Flush activation assemblies for carpet and tile. Aesthetically pleasing assemblies are interchangeable for both cast-iron and stamped steel.

A wide selection of data and bezel options available for use with Ortronics TracJack and Series II devices.

Fully adjustable box. Before and after concrete pour adjustability. Lower installed cost.


Boxes and covers have been listed by Underwriters Laboratories Inc. to their standard UL514A, 514C, 514D, and Canadian standard C22.2

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point-of-use.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786564221746	Country Of Origin	Mexico
Construction	Assembled	Cover Style	Flush
Number of Knockouts	2	Application Sector	Commercial, Education

Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. Meets Article 314.27(C) of NEC.		Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box			
Dimensions				
Product Width US	7.0 in	Product Weight US	4.622 lb	
Product Volume US	240.63 cu in	Product Depth US	13.75 in	
Product Height US	2.5 in	Cubic Capacity	126 in³	
Knockout Size	1/2 in, 3/4 in			
Listing Agencies / 3rd Party Agencies				
ULus ListingNumber	E2961	cULus Listed	Yes	
Trade Programs				
USMCA	Yes			
Additional Information				
RoHS Compliant	Yes	Product Environmental Profile	Yes	
Technical Information				
Floor Type	Concrete	Service Capacity	Triple	
Box Capacity	3 Gangs	Cable Entry	knockout	
Box Type	Above-Grade	Number of Outlets	0	
Depth Behind Device Plates	1.75 in			