



radiant Collection
radiant® Tamper-Resistant Outlet, Graphite
Part No. 885TRGCC12



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Indoor, Residential, Tamper-Resistant	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Is Tamper-Resistant Yes Amperage 15 A

Number of Poles Double Pole Indoor/Outdoor Indoor

NEMA Configuration Code 5-15R Mounting Type Box

Voltage 125.0 V Environmental Conditions 95% (relative humidity, non-condensing)
