



Pass and Seymour  
Wide Slide Series Fan Speed Control, Ivory  
Part No. 94084I

1.5A Slide De-Hummer Fan Control



## Features & Benefits

Through the use of specially designed capacitive circuitry, these units can control fans at 3- or 4-speed levels in slide, rotary, and dual styles with virtually no fan motor noise.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007940824
Country Of Origin	Mexico	Features	Fan Control
Application Sector	Residential	Standard	CSA Listed, UL Listed

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

### Technical Information

Connection	Pigtail Leads	Contact Rating	120V
Amperage	1.5 A	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Speed Range	Variable
Environmental Conditions	Indoor Only		