



Cablofil
CabloPort Block 20" Long [943525]
Part No. 943525



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Cable pathway or other products mounted to base with clamps and screws.

Install: on any roofing material or other flat surface.

Curb style: maximum load 500 lbs. (CP5 - maximum load 150 lbs.).

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Composite material: allows through bolts or lag type screws (through bolts recommended)

Specifications

General Info

Product Line	Cablofil	Finish	AT
UPC Number	800388019102	Country Of Origin	Canada
Application Sector	Commercial	Type	Fasteners

Dimensions

Product Width US	6.0 in	Product Weight US	9.3 lb
Product Volume US	0.271 cu ft	Product Depth US	19.5 in
Product Height US	4.0 in		

Trade Programs

BAA	Yes
-----	-----
