

Timer, 30min 1hp 20a 125v/10a 250-277volt, No Hold, Ivory



Features & Benefits

Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.

Quiet operation.

Available with or without hold.

Easily installed.

Accurate to +/- 5 percent.

Energy saving.

Turning clockwise causes unit to time load off after desired time delay.

Time range from 5 minutes to 12 hours.

Decorator styling.

Large head screw terminals.

Motor rated.

Specifications

General Info

Color	Ivory
UPC Number	785007970302
Country Of Origin	China
Product Line	Pass & Seymour
Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
CSA Listed	Yes
CSA File Number	074656
cULus ListingNumber	103624

Technical Information

Voltage 125 V

Connection Back & Side Wired

Coil Voltage 120VAC @ 60Hz

Timing Range 30 minutes

Action Single Pole
