



On-Q
Premium High Speed HDMI™ Cable with Ethernet (7m)
Part No. AC2AP7BK



The 18Gbps Premium Certified HDMI Cable with Ethernet complies with the HDMI 2.0b specification and features an anti-counterfeit label for authenticity. It supports 18.2Gbps bandwidth, UltraHD 4K@60Hz, HDR, Deep Color, ARC, and Ethernet. The cable meets the CSA FT4 Vertical Flame Test, with a max char height of 59 inches, more stringent than the UL1685 test. Enhanced retention clips require 4.5 lbs of pulling force to remove, and the small over-mold allows for easier pulling between studs or through articulating mounts. Rated CMG, CL2/CL3, these in-wall rated cables are resistant to carrying flame and can handle surges up to 300 watts.

Features & Benefits

Premium HDMI Certified to comply with the HDMI 2.0b specification and marked with the anti-counterfeit label to ensure authenticity

Supports: 18.2Gbps bandwidth, UltraHD - 4k@60Hz, High Dynamic Range (HDR), Deep Color, ARC, Ethernet

Meets CSA FT4 Vertical Flame Test - This testing procedure has cables mounted on a vertical tray, which are then exposed for 20 minutes to a 70,000 BTU/hour flame

The FT4 max char height of 59 inches is more stringent than the UL1685 vertical tray flame test max char height of 78 inches

Enhanced retention clips to keep the cable firmly in place, requiring 4.5 lbs of pulling force to remove

Small over-mold for easier pulling between studs or through articulating mounts

Rated: CMG, CL2/CL3 – These cables are in-wall rated, resistant to carrying flame, and can carry a surge of up to 300 watts

Ideal applications: residential home theater, flat panel installations

Available in lengths from 1 to 7 meters

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Specifications

General Info

Product Line	On-Q	Color	Black
UPC Number	804428431954	Country Of Origin	China

Dimensions

Product Length US 22.9 FT

Technical Information

Connector	HDMI Type A to Type A, 4-contacts, 24K Gold-plated	Number of Pins	19
-----------	--	----------------	----

Data Transfer Rate	18.6 Gbps
--------------------	-----------
