



On-Q  
Cat 6 Patch Cable, 7 ft, Blue  
Part No. AC3607BEV1



This component rated Cat 6 patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application. These patch cables are 100% tested and exceed the patch cable standard

## Features & Benefits

250 MHz patch cable fully supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.

## Specifications

### General Info

Product Line	On-Q	Color	Blue
UPC Number	804428066835	Country Of Origin	China

### Dimensions

Product Length US	7.0 FT
-------------------	--------

### Technical Information

Jacket Material	PVC	Wire Gauge	24 AWG
Cable Type	Cat6	Cable Diameter	0.25 in