



On-Q
8K Ultra High Speed HDMI™ Cable, 3m
Part No. AC8K3MBK

8K ULTRA HIGH SPEED HDMI™ CABLE



This Ultra High-Speed (48Gbps) HDMI cable supports 8K at 60Hz and 4K at 120Hz. It is CL3/FT4 rated for in-wall use and features a Sure Grip connector to prevent cable damage. Enhanced retention clips keep the cable firmly in place, and the gold-plated connector resists corrosion while providing the highest level of signal conductivity. The Enhanced Audio Return Channel (eARC) supports high-bitrate audio formats including DTS-HD Master Audio, DTS:X, Dolby TrueHD, and Dolby Atmos.

Features & Benefits

Supports 8K at 60Hz and 4K at 120Hz

CL3/FT4 Rated for in-wall use

Sure Grip connector provides a firm grip to prevent cable damage

Enhanced retention clips keep the cable firmly in place

Gold Plated Connector resists corrosion and provides the highest level of signal conductivity

Enhanced Audio Return Channel (eARC): Supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Specifications

General Info

Product Line	On-Q	Color	Black
Finish	Matte	UPC Number	804428435051
Country Of Origin	China		

Dimensions

Product Width US	0.87 in	Product Weight US	0.55 lb
Product Height US	10.16 in	Product Length US	8.66 in

Technical Information

Video Resolution	8K 60Hz	Jacket Application	In-Wall Rated
------------------	---------	--------------------	---------------

Cable Type	Ultra High Speed HDMI	Jacket Rating	CL3 Rated, FT4 Rated
Data Transfer Rate	48 Gbps	Connector Type	HDMI
Video Input Support	HDMI	Conductor Material	Gold
Environmental Conditions	0.9		