



adorne Collection
adorne® 0-10V sofTap® Dimmer, Magnesium, with Microban®
Part No. ADTP4FBL3PM4



Turn lights on/off, or even adjust the light level, with just a soft tap of a finger thanks to inventive micro-movement technology. Use this dimmer switch on its own to control a 0-10V light or fixture from a single location, or pair with a remote dimmer switch for 3-way control a single light source from two locations.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable 0-10V bulbs or fixtures. Perfect for adding precise light level control -- all it takes is a soft tap to turn on/off or adjust brightness.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	China	Features	Antimicrobial Protection, Indicator Lights
Switch Type	sofTap	Number of Switches	1
Standard	cULus	Warranty Type	Limited Lifetime Warranty

Type	Dimmer
------	--------

Dimensions

Product Width US	1.77 in	Product Depth US	1.62 in
Product Height US	1.77 in		

Technical Information

Electrical Rating	120V 10A (0-10V Fluorescent), 120V 10A (0-10V LED)	Connection	Screw Terminals
Number of Gangs	1	Bulb Compatibility	Fluorescent, LED
Number of Poles	3-Way, Single Pole	Wattage	1100 W
Mounting Type	Box	Voltage	0 to 10 V
Connection Type	Internal Pressure Plates	Load	Fluorescent, LED