



adorne Collection  
adorne® 0-10V sofTap® Dimmer, White, with Microban®  
Part No. ADTP4FBL3PW4



Turn lights on/off, or even adjust the light level, with just a soft tap of a finger thanks to inventive micro-movement technology. Use this dimmer switch on its own to control a 0-10V light or fixture from a single location, or pair with a remote dimmer switch for 3-way control a single light source from two locations.

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable 0-10V bulbs or fixtures. Perfect for adding precise light level control -- all it takes is a soft tap to turn on/off or adjust brightness.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007055948
Country Of Origin	China	Features	Antimicrobial Protection, Locator Light, Low-End Trim (Dim Range)
Switch Type	Digital, Single Pole 3-Way, sofTap	Number of Switches	1

Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Commercial, Hospitality, Residential	Standard	cULus
Warranty Type	Limited Lifetime Warranty	Type	Dimmer
Dimensions			
Product Width US	1.77 in	Product Depth US	1.62 in
Product Height US	1.77 in		
Technical Information			
Load Rating	120V 10A (Fluorescent), 120V 10A (LED), 277V 5A (Fluorescent), 277V 5A (LED)	Dimming Compatibility	0-10 V
Frequency Rating	60 Hz	Number of Gangs	1
Bulb Compatibility	Fluorescent, LED	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Trim/Adjustment Level	Button
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads (0-10V), Screw Terminals
Voltage	120/277 VAC		