



Turn lights on or off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, this dimmer switch self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V). Always adjust to the precise light level you want, without the flicker.

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology	For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.
Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.	Perfect for adding precise light level control – all it takes is a soft tap to turn on/off or adjust brightness.
Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).	Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.
Usable in both single-pole and 3-way applications.	More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007023176

Country Of Origin	China	Features	Antimicrobial Protection, Auto-Calibration (Trim), High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)
Switch Type	Digital, Single Pole 3-Way, sofTap	Number of Switches	1
Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Commercial, Hospitality, Residential	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		
<b>Dimensions</b>			
Product Width US	1.79 in	Product Depth US	1.77 in
Product Height US	4.2 in		
<b>Technical Information</b>			
Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward or Reverse Selectable Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, Incandescent, LED
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Button	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC