



adorne Collection
adorne® sofTap™ Wi-Fi Ready Remote Dimmer
Part No. ADTPRRM1



Working in conjunction with an adorne Hub and a sofTap Wi-Fi Ready Master Dimmer for 3-way control. Use the dimmer to turn lights on/off, or adjust brightness, all with just the lightest tap of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Dimmer, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Dimmer via the easy-to-follow instructions.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Color	Magnesium	UPC Number	804428065722
Country Of Origin	United States	Product Line	Pass & Seymour
Number of Switches	1	Application Sector	Residential
Warranty Type	1-Year Limited Warranty	Standard	cULus, FCC, UL 1472

Dimensions

Product Width US	1.77 in	Product Length US	4.2 in
Product Depth US	1.79 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Number of Poles	Single Pole, 3-Way, Multi-Location	Number of Gangs	1
Voltage	120 V	Mounting Type	Box
Frequency Rating	900 M (RF) Hz	Load	Auxiliary Remote Dimmer - No Load
Connection Type	Internal Pressure Plates	Environmental Conditions	0 to 80 (relative humidity, non-condensing)
