



adorne Collection
adorne® Whisper® Tru-Universal Dimmer, Magnesium, with Microban®
Part No. ADWR703TUM4



The whisper-control modern dimmer switches from the adorne Collection allow you to control lights with a soft, fluid motion. Integral silver contacts provide long-lasting performance. A self-calibrating Tru-Universal Dimmer, this dimmer switch works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

| | |
|---|--|
| Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology | For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes. |
| Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required. | Control lights with a fluid, whisper-soft toggle motion to turn on/off, or use the smooth slider to dim or brighten to your preferred light level. |
| Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V). | Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance. |
| Usable in both single-pole and 3-way applications. | More color options available to fit any style, including finishes to match current hardware and lighting trends. |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|--------------------------|
| Product Line | Pass & Seymour | Color | Magnesium |
| Country Of Origin | China | Features | Antimicrobial Protection |
| Switch Type | Whisper | Number of Switches | 1 |

| | |
|---------------|---------------------------|
| Warranty Type | Limited Lifetime Warranty |
|---------------|---------------------------|

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.77 in | Product Depth US | 1.2 in |
| Product Height US | 4.19 in | | |

Technical Information

| | | | |
|--------------------|---|-----------------|--------------------------|
| Electrical Rating | 120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL) | Number of Gangs | 1 |
| Bulb Compatibility | CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon | Number of Poles | 3-Way, Single Pole |
| Wattage | 700 W | Mounting Type | Box |
| Voltage | 120.0 V | Connection Type | Internal Pressure Plates |