




Wiremold
AF1 Series Raised Floor Box
Part No. AF1-NT



The AF1 Raised Floor and Stage Floor Box provides three separate compartments that accommodate a combination of power, communication and audio/video devices. This combination is accomplished with the built-in service dividers. These dividers are arranged in a single-double, single-gang configuration. Die-cast aluminum housing provides added strength and reliability.

Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as color choice of black, brown, or gray. NOTE: AF1 Floor Boxes are available in a prewired (power only) version. Consult factory for ordering information. For information on prewired versions with Walkerflex, see the Walkerflex Pages of this website. All boxes and plates are sold separately.

Features & Benefits

The AF1 Raised Floor and Stage Floor Box provides three separate compartments that accommodate a combination of power, communication and audio/video devices.

Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as color choice of black, brown, or gray.

This combination is accomplished with the built-in service dividers. These dividers are arranged in a single-double, single-gang configuration. Die-cast aluminum housing provides added strength and reliability.

NOTE: AF1 Floor Boxes are available in a prewired (power only) version. Consult factory for ordering information. For information on prewired versions with Walkerflex, see the Walkerflex Pages of this website. All boxes and plates are sold separately.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564519294
Country Of Origin	United States	Construction	Assembled
Cover Material	Polycarbonate	Application Sector	Commercial
Standard	UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Weight US	5.0 lb	Cubic Capacity	208.6 in ³
-------------------	--------	----------------	-----------------------

Knockout Size	1/2 in, 3/4 in
---------------	----------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Carpet, Raised, Tile	Service Capacity	Triple
------------	----------------------	------------------	--------

Minimum Floor Depth	5 in	Box Capacity	4 Gangs
---------------------	------	--------------	---------

Cable Entry	Through Floor	Box Type	Recessed
-------------	---------------	----------	----------

Depth Behind Device Plates	2.75 in
----------------------------	---------