



Pass and Seymour
15A Tamper-Resistant AFCI Receptacle, Gray
Part No. AF153TRGRY

15A Arc Fault Circuit Interuption Receptacle

Specifications

General Info

| | | | |
|-----------------------|--|-------------------------|-------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | AF152TRGRY |
| Color | Gray | Finish | Matte |
| UPC Number | 785007382587 | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | AFCI, Tamper-Resistant |
| Application Sector | Commercial, Multi-Dwelling Unit, Residential | Wall Plate Included | Yes |
| Standard | UL | Warranty Type | 1-Year Limited Warranty |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E135325 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

| | | | |
|-------------------------|-------------|----------------------|---|
| Is Tamper-Resistant | Yes | Connection Location | Back and Side |
| Number of Wires | 3 | Amperage | 15 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
| NEMA Configuration Code | 5-15R | Wire Connection Type | Internal Pressure Plates, Screw Terminals |
| Voltage | 125.0 V | | |