



Wiremold  
TR PLGMD 6FT. SGL CRT 12IN. OC  
Part No. AL20GB612TR



Plugmold® Multioutlet Systems are now available with multiple USB charging options that provide power and charging for any application. The tamper-resistant receptacles prevent the insertion of foreign objects and reduce the risk of shock or electrocution. Meets 2014 NEC section 406 requirements.

## Features & Benefits

Compact, low profile appearance.

Installed power and USB charging in multiple lengths to meet space and location requirements

USB Charging.

Tamper-resistance protection.

Single, alternating circuit, and isolated ground wiring options available.

Plugmold products can be modified to accommodate virtually any application or aesthetic need.

Custom solution available for large or specific use electrical installations.

## Specifications

### General Info

Product Line	Wiremold	Color	Aluminum
UPC Number	786776195545	Country Of Origin	United States
Product Series	AL2000 Series	Number of Receptacles	6
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Plugmold
Installed Devices	Single Receptacle		

### Dimensions

Product Width US	1.42 in	Product Weight US	3.6 lb
------------------	---------	-------------------	--------

Product Depth US	1.13 in	Product Length US	1.42 in
Receptacle Spacing	12 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Is Pre-Wired	Yes	Wiring Configuration	Single Circuit
Amperage	15 A	Indoor/Outdoor	Indoor
Wiring Method	Hard-Wired	NEMA Configuration Code	5-15R
Mounting Type	On Surface	Voltage	125.0 V