



Approved Networks

Juniper EX-SFP-1GE-FE-E-T Compatible 10/100/1000Base-TX SFP Transceiver (Copper, 100m, RJ-45, Non-DDM, C-Temp)

Part No. EXSFP-1GE-FE-E-T-A

Juniper EX-SFP-1GE-FE-E-T Compatible 10/100/1000Base-TX SFP Transceiver (Copper, 100m, RJ-45, Non-DDM, C-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Approved Networks	Color	Silver
Country Of Origin	China	OEM Manufacturer	Juniper
Features	Auto-Negotiation	Application Sector	Commercial, Data Center, Industrial
Standard	IEEE 802.3u	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	13.66 mm	Product Weight US	0.4 oz
Product Depth US	80.77 mm	Product Height US	13.97 mm

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Max Distance Support	100 m	Operating Temperature Min	-40 °C
Protocol	Ethernet	Operating Temperature Max	85 °C
Media Type	Copper	Data Transfer Rate	1.25 Gbps
Connector Type	RJ-45	Form Factor	SFP-T

Operating Temperature

0°-70°C
