




adorne Collection  
adorne® 20A Tamper-Resistant Dual-Controlled Outlet, White  
Part No. ARCD202W10



A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Independently cut power to either plug when not in use to conserve energy.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

|                        |                  |                       |                           |
|------------------------|------------------|-----------------------|---------------------------|
| Product Line           | Pass & Seymour   | Color                 | White                     |
| Finish                 | Matte            | UPC Number            | 785007050691              |
| Country Of Origin      | China            | Number of Receptacles | 2                         |
| Device Front Face Size | Full-Size        | Device Backbody Size  | Full-Size                 |
| Outlet Type            | Tamper-Resistant | Application Sector    | Residential               |
| Standard               | CULUS            | Warranty Type         | Limited Lifetime Warranty |
| Type                   | Outlet           |                       |                           |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.77 in | Product Depth US | 1.73 in |
| Product Height US | 2.12 in |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |                          |                          |   |
|---------------------|--------------------------|--------------------------|---|
| Is Tamper-Resistant | Yes                      | Phase                    | Single                                  |
| Connection          | Side and Back Wire       | Number of Wires          | 3                                       |
| Number of Gangs     | 1                        | Amperage                 | 20 A                                    |
| Number of Poles     | Double Pole              | Wire Size                | 14 - 10 AWG                             |
| Indoor/Outdoor      | Indoor                   | Mounting Type            | Box                                     |
| Connection Type     | Internal Pressure Plates | Environmental Conditions | 95% (relative humidity, non-condensing) |