



adorne Collection
adorne® 15A Paddle™ Switch, Engraved - Nightlight, Magnesium
Part No. ASPD1532MENL



A modern twist on classic up-and-down switch control, the Paddle Switch lets you turn lights on and off with ease. Use this device on its own to control a light or fixture from a single location, or pair with a second switch or dimmer to control a single light source from two locations. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a Laser engraved at the factory with the word "Nightlight" range of contemporary colors and stunning finishes.

Perfect for anywhere you'd like to upgrade the look of a standard switch.

Pair with matching Paddle Dimmer or Paddle Fan Speed Control to create a uniform look throughout a room

Use on its own to control a light from one location (single-pole operation) or pair with a second switch or dimmer to control a single light source from two locations (three-way operation)

This item also comes in 20A and 20A 4-Way options.

This item is also available in Magnesium.

Specifications

General Info

| | | | |
|------------------------|----------------|----------------------|---------------------------|
| Product Line | Pass & Seymour | Color | Magnesium |
| Finish | Frosted | UPC Number | 785007135077 |
| Country Of Origin | China | Features | Engraved |
| Device Front Face Size | Full-Size | Device Backbody Size | Full-Size |
| Application Sector | Residential | Warranty Type | Limited Lifetime Warranty |

Dimensions

| | | | |
|------------------|---------|------------------|--------|
| Product Width US | 1.77 in | Product Depth US | 1.5 in |
|------------------|---------|------------------|--------|

| | |
|-------------------|---------|
| Product Height US | 1.77 in |
|-------------------|---------|

Technical Information

| | | | |
|------------|-----------------|-----------------|--------------------------|
| Connection | Screw Terminals | Amperage | 15 A |
| Wire Size | #14 - #10 AWG | Connection Type | Internal Pressure Plates |