



adorne Collection
adorne® Engraved Paddle™ Switch, 20A, Nightlight, Magnesium
Part No. ASPD2032MENL



A modern twist on classic up-and-down switch control, the Paddle Switch lets you turn lights on and off with ease. Use this device on its own to control a light or fixture from a single location, or pair with a second switch or dimmer to control a single light source from two locations. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a Laser engraved at the factory with the word "Nightlight" range of contemporary colors and stunning finishes.

Perfect for anywhere you'd like to upgrade the look of a standard switch.

Pair with matching Paddle Dimmer or Paddle Fan Speed Control to create a uniform look throughout a room

Use on its own to control a light from one location (single-pole operation) or pair with a second switch or dimmer to control a single light source from two locations (three-way operation)

This item also comes in 15A and 15A 4-Way options.

This item is also available in Magnesium.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007135138
Country Of Origin	China	Features	Engraved
Device Front Face Size	Full-Size	Device Backbody Size	Full-Size
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.77 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

Product Height US	1.77 in
-------------------	---------

Technical Information

Connection	Screw Terminals	Amperage	20 A
------------	-----------------	----------	------

Wire Size	#14 - #10 AWG	Connection Type	Internal Pressure Plates
-----------	---------------	-----------------	--------------------------