



Wiremold
AV3 Flush AV Assembled Poke-Thru Assembly, Black
Part No. AV3ATCBK



A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes one adapter to accept Legrand AVIP or Extron Electronics MAAP mini architectural adapter plates, Wiremold Open System adapters, and Ortronics TracJack and Series II mounting adapters. Modular Jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. AV3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Features & Benefits

A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground	Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS)
Aluminum and brass flanges standard with black cover	Aluminum flange also available with an aluminum colored nonmetallic cover (AA)
Brass flange also available with brass colored nonmetallic cover (AB)	Modular Jacks sold separately
Modular Jacks sold separately	NOTE: Assembled with scrub water gasket
For use on tile or carpet floors	AV3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole
Not designed to work with bare concrete or terrazzo	For use on tile or carpet floors

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564015598	Country Of Origin	Mexico
Number of Knockouts	2	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		

Dimensions

Product Width US	8.25 in	Product Weight US	6.619 lb
Product Volume US	1157.06 cu in	Product Depth US	17.0 in
Product Height US	8.25 in	Cubic Capacity	24.5 in ³
Core Hole Size	4 in	Knockout Size	1-1/4 in, 3/4 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Floor Type	Carpet, Tile, Wood	Service Capacity	Dual
Fire Rating	2 hr	Number of Outlets	2