

## USAGE

- ◆ Perfect anywhere you'd like to upgrade the look of a standard wall switch, dimmer switch or outlet.
- ◆ The adorne 1-Gang Wall Plate is perfectly sized to fit two Half-Size USB Outlets, a single Pop-Out or Standard Outlet, and any adorne Switch or Dimmer Switch.
- ◆ The design has no visible screws and features an easy, universally appealing satin light almond finish.
- ◆ This product comes in [dozens of finishes](#), including a variety of luxurious metals, or order in your own custom finish.
- ◆ This item is available in 1-6-gang capacities. [Shop now](#) to find the right Wall Plate for your home.

## Features & Benefits

A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile. Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.

Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals. Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.

## Specifications

### General Info

|                    |                        |              |                                   |
|--------------------|------------------------|--------------|-----------------------------------|
| Product Line       | Pass & Seymour         | Color        | Light Almond                      |
| Country Of Origin  | Mexico                 | Construction | Screwless Design Snaps into Frame |
| Application Sector | Residential/Commercial | Standard     | cULus UL514, cETLus               |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 3.45 in | Product Depth US | 0.35 in |
|------------------|---------|------------------|---------|

---

Product Height US      5.13 in

---

### Technical Information

---

Cutout                      Square                                      Thickness                      0.07 in

---

Orientation                      Horizontal

---