adorne Collection

adorne® Magnesium 2-Gang Screwless Wall Plate with Microban®

Part No. AWP2GMG4



Pair with devices in the same Magnesium finish for a stunning monochromatic statement. Made exclusively for use with designer switches and outlets from the adorne® Collection. This wall plate* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product. * Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology.

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.

Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.

Includes one Wall Plate and one Steel Frame for mounting the wall plate.

A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.

Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007050745
Country Of Origin	Mexico	Material	Polycarbonate
Product Type	Wall Plate	Construction	Plastic
Features	Antimicrobial Protection	Wall Plate Type	Dimmer/Switch, Outlet
Application Sector	Commercial, Residential	Standard	cULus UL514, cETLus
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	5.29 in	Product Depth US	0.35 in
Product Height US	5.13 in		

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Screwless
Orientation	Vertical		