



Wiremold  
20GB606TRUSB 6' Plugmold® Multioutlet System with USB  
Part No. BK20GB606TRUSB



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

## Features & Benefits

USB charging. 2.4A USB type A receptacle charges faster than other USB receptacles and is compatible with USB 2.0 and 3.0 type devices.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

This product meets the material restrictions of RoHS.

Tamper-resistant receptacles. Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code® Tamper-Resistant requirements.

Compact design. Eliminates the need for bulky AC adapters.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786776182552	Country Of Origin	United States
Product Series	2000 Series	Number of Receptacles	11
Features	USB-A Charging	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail	Standard	cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC.

Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Plugmold
Installed Devices	Single Receptacle, USB-A Ports		
Dimensions			
Product Width US	1.3 in	Product Weight US	3.78 lb
Product Depth US	0.75 in	Product Length US	1.3 in
Receptacle Spacing	6 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Is Pre-Wired	Yes	USB Wattage	15 W
USB Amperage	2.4 A	Wiring Configuration	Single Circuit
Number of USBs	1	Amperage	15 A
Indoor/Outdoor	Indoor	Wiring Method	Hard-Wired
NEMA Configuration Code	5-15R	Mounting Type	On Surface
Voltage	125.0 V	Environmental Conditions	Dry interior locations