



Pass and Seymour
Strain Relief Grips
Part No. BOX52

Wide range, Straight male, Dust tight grips. 3/4-inch NPT, 0.520-inch-0.730-inch.



Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

450 lbs breaking strength rating (in US lbs)

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | Type | Dust Tight |

Dimensions

| | | | |
|------------------|---------|-------------------|---------|
| Product Width US | 0.73 in | Product Length US | 0.75 in |
|------------------|---------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

Technical Information

| | | | |
|---------------------|---------|---------------------|---------|
| Maximum Cable Range | 0.52 in | Minimum Cable Range | 0.73 in |
|---------------------|---------|---------------------|---------|

| | | | |
|----------|--|----------|---|
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure. | | |