



**Pass and Seymour**  
Strain Relief Grips  
Part No. BOX70

Wide range, Straight male, Dust tight grips. 1" NPT, 0.700-0.970"



### Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and power centers.

Includes insulated bushing.

700 lbs breaking strength rating (in US lbs)

### Specifications

#### General Info

|              |                                   |                    |   |
|--------------|-----------------------------------|--------------------|---|
| UPC Number   | 785007996180                      | Country Of Origin  | Mexico  |
| Product Line | Pass & Seymour                    | Application Sector | Industrial  |
| Type         | Dust Tight                        | Construction       | Various Types of Pulling, Support and Strain Relief Grips |
| Standard     | UL/CSA Approval (consult factory) |                    |   |

#### Listing Agencies / 3rd Party Agencies

|            |     |                 |       |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

#### Technical Information

|          |  |            |  |
|----------|--|------------|--|
| Mounting | Consult the Factory for Mounting Recommendations | Cable Size | NPT Size: 1; Cable Dia. Range: 0.700-1.000   |
| Capacity | Various Cable Diameter Ranges                    | Load       | Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure. |