



Features & Benefits

Field configurable wall plate system.

Adjustable top end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Application Sector	Commercial
Standard	RoHS, cULus, UL Listed	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Number of Poles	Single Pole	Wattage	1100 W
Voltage	120.0 V	Load	Incandescent
Environmental Conditions	Humidity: Less than 95% non condensing		