



Pass and Seymour
Discontinued - Titan Series Fluorescent 3 Wire Dimmer, White
Part No. CD3FB163PW



Slide Dimmer, Electronic Single Pole/3Way 3Wire PRESET 16A120V, White

Features & Benefits

For use with 3 wire 120V and 277V fluorescent dimming ballasts.

Labeling system

Shipped with protective film

Superior ratings with a minimum of derating when ganged

Available in single pole slide-to-OFF and single pole/3-way preset models

Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system

Field configurable wall plate system

Adjustable low end output voltage

Rugged construction

Simple to plan the rough-in

Attractive European styling. Eye-catching packaging

Blank center plate included

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	16 A	Voltage	120.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%