



Pass and Seymour
Discontinued - Titan Series Fluorescent 4 Wire Dimmer, Brown
Part No. CD4FB



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

Features & Benefits

| | |
|---|--|
| Field configurable wall plate system | Labeling system |
| Adjustable low end output voltage | Shipped with protective film |
| Rugged construction | Superior ratings with a minimum of derating when ganged |
| Simple to plan the rough-in | Available in single pole slide-to-OFF and single pole/3-way preset models |
| Attractive European styling. Eye-catching packaging | Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system |
| Blank center plate included | Requires BZ50 24 VDC Power Pack |

Specifications

General Info

| | | | |
|-------------------|--------------------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Brown |
| Country Of Origin | China | Application Sector | Commercial |
| Standard | cULus, California Title 24 Compliant | Type | Dimmer |

Technical Information

| | | | |
|------------------|--|--------------------------|---|
| Operating Cycles | 100 | Frequency Rating | 60 Hz |
| Number of Poles | Single Pole | Voltage | 24.0 V |
| Load | Up to rating of device (including de-rating) | Environmental Conditions | Non-Condensing Humidity: Less than 95% |