



Pass and Seymour
Discontinued - Titan Series Fluorescent 3-Way, Preset 4 Wire Dimmer, White
Part No. CD4FB3PW



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

Features & Benefits

Field configurable wall plate system	Labeling system
Adjustable low end output voltage	Shipped with protective film
Rugged construction	Superior ratings with a minimum of derating when ganged
Simple to plan the rough-in	Available in single pole slide-to-OFF and single pole/3-way preset models
Attractive European styling. Eye-catching packaging	Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system
Blank center plate included	Requires BZ50 24 VDC Power Pack

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	10 A	Voltage	24.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%