



Pass and Seymour
Discontinued - Titan Series LED 4-Wire Single-Pole/3-Way Preset Dimmer, Light Almond
Part No. CD4FBL3PLA



Features & Benefits

Includes integrated power pack and blank center plate.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

For covering patents, see www.legrand.us/patents.

Field configurable wall plate system.

Adjustable low end trim.

Rugged construction.

Simple to plan the rough-in.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Commercial	Standard	RoHS, cULus
Type	Dimmer		

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	10 A	Voltage	120.0 V
Load	Fluorescent	Environmental Conditions	Humidity: Less than 95% non condensing