



SLIDE CONTROL 1.6A DEHUMMER, IVORY

Features & Benefits

Field configurable wall plate system.

Shipped with protective film.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

Blank center plate included.

Labeling system.

Rugged construction.

Available in single pole slide-to-OFF models.

Eye-catching packaging.

Available in both continuously variable and de-hummer styles.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Commercial
Standard	cULus		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	50	Amperage	1.6 A
------------------	----	----------	-------

Number of Poles

Single Pole

Voltage

120.0 V

Environmental Conditions

Non-Condensing Humidity: Less than 95%
