



Pass and Seymour
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, White
Part No. CDFB10277W

Slide Dimmer, Electronic Single Pole 2Wire 10A 277V, White



Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.

Field configurable wall plate system.

Labeling system.

Adjustable low end output voltage.

Shipped with protective film.

Rugged construction.

Superior ratings with a minimum of derating when ganged.

Simple to plan the rough-in.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Attractive European styling.

Eye-catching packaging.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

Blank center plate included.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	10 A	Number of Poles	Single Pole
Voltage	277.0 V	Load	Up to rating of device (including de-rating)
Environmental Conditions	Non-Condensing Humidity: Less than 95%		
