



Pass and Seymour
Titan Series Fluorescent 2 Wire Dimmer, Black
Part No. CDFB163PBK

Slide Dimmer, Electronic Single Pole/3Way 2Wire PRESET 16A, Brown



Features & Benefits

- For use with 2 wire 120V and 277V fluorescent dimming ballasts.
- Labeling system.
- Shipped with protective film.
- Superior ratings with a minimum of derating when ganged.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Eye-catching packaging.
- Blank center plate included.
- Field configurable wall plate system.
- Adjustable low end output voltage.
- Rugged construction.
- Simple to plan the rough-in.
- Attractive European styling.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system. [See Page N-29.]
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Black	UPC Number	785007303193
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Commercial	Type	Dimmer
Standard	cULus, California Title 24 Compliant		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Voltage	120 V	Frequency Rating	60 Hz
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95
Operating Cycles	100		