



Pass and Seymour  
**Discontinued - Titan Series Fluorescent 2 Wire Dimmer, Ivory**  
Part No. CDFB163PI



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

## Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts	Field configurable wall plate system
Labeling system	Adjustable low end output voltage
Shipped with protective film	Rugged construction
Superior ratings with a minimum of derating when ganged	Simple to plan the rough-in
Available in single pole slide-to-OFF and single pole/3-way preset models	Attractive European styling. Eye-catching packaging
Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system	Blank center plate included

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	16 A	Voltage	120.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%

---