



Pass and Seymour  
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, Gray  
Part No. CDFB53PGRY



## Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	5 A	Voltage	120.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%

---