



Features & Benefits

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Product Line

Pass & Seymour

Color

Black

Country Of Origin

China

Application Sector

Commercial

Standard

cULus, California Title 24
Compliant

Type

Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber

95219

cULus Listed

Yes

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	1600 A	Number of Poles	Single Pole
Voltage	120.0 V	Load	Up to rating of device (including de-rating)
Environmental Conditions	Non-Condensing Humidity: Less than 95%		
