



Pass and Seymour
Discontinued - Titan Series Magnetic Low-Voltage Dimmer, Gray
Part No. CDLV1603PGRY

Slide Dimmer, Low Voltage, Single Pole/3Way PRESET 1600VA, Gray



Features & Benefits

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	1600 A	Voltage	120.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%
