



Pass and Seymour
Strain Relief Deluxe Cord Grips, 1-1/4-in NPT, Straight Male
Part No. CG1022

Cord Grip Male Straight, 1-1/4-inch NPT, 1.250-inch-1.375-inch



Features & Benefits

Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.

They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain.

They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.

Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007996593
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Dimensions

Product Width US	1.375 in
------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	1.25 in	Minimum Cable Range	1.375 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations