



Pass and Seymour
Aluminum Cord Grip, 2 1/2-in Straight, 2.06-2.19 OD Range, Form Size 7
Part No. CG25021887



Deluxe Aluminum Cord Grips are UL Listed and CSA Certified for use in both indoor and outdoor applications to prevent cable pullout, to control arc of bend, and to provide a tight seal against environmental elements such as dirt, moisture and coolants. Cord grips are available in a wide range of conduit sizes from 1/4" to 3" in straight, 90 and 45 styles. A uniquely designed combination tightening surface with both a hex area and a knurled surface provides extra gripping for initial hand tightening.

Features & Benefits

A unique design with a combination tightening surface that includes both a hex area and knurled surface providing extra gripping for initial hand tightening and ease of installation

Anti-friction washer that fits between the nut and bushing for easier compression and a tight seal

Available in straight, 45°, and 90° styles

All aluminum design offers corrosion resistance and industrial strength for heavy duty applications

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007065862
Country Of Origin	United States	Construction	Aluminum Cord Grip
Application Sector	Commercial, Industrial	Standard	UL Listed, CSA Listed
Type	Cord Grip		

Dimensions

Cable Diameter Range	1.68-1.81 in
----------------------	--------------

Technical Information

Maximum Cable Range	1.68 in	Grip Angle	Straight
Minimum Cable Range	1.81 in	Form Size	F7

Indoor/Outdoor	Both	NPT Thread Size	2-1/2 in
----------------	------	-----------------	----------