



Pass and Seymour
Discontinued - Nylon Cord Grip, 3/4-in NPT Straight, .500-.625 OD Range
Part No. CGN75500BK



Non-Metallic Cord Connectors are constructed of a durable, nylon material which offers excellent corrosion resistance, is lightweight, durable and ideal for use in damp environments. Nylon Cord Connectors are ideally suited for use in applications with moisture or washdowns and they provide an environmental seal against dirt, coolants, as well as other chemicals.

Features & Benefits

Heavy duty Nylon body is resistant to impact and corrosion

Available in straight, 90°, and underground feed styles

Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical

Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals

Color coded grommets make for easy identification and ease of installation

Specifications

General Info

Product Line	Pass & Seymour	Finish	Matte
Country Of Origin	India	Construction	Nylon Body with Color-Coded Rubber Grommets
Application Sector	Commercial/Industrial	Type	Cable Management

Technical Information

Maximum Cable Range	0.687 in	Minimum Cable Range	0.562 in
---------------------	----------	---------------------	----------