



On-Q
Discontinued - Outdoor 1080 IR Dome Camera with Zoom
Part No. CM7020



Keep a watchful eye on your home with Legrand's CM7020 Dome Camera. It delivers full 1080p HD and has professional-grade night vision. The durable dome housing is vandal and weather resistant and the varifocal lens allows for motorized remote zooming.

Features & Benefits

- Enclosure-mounted recording solution for up to four IP cameras
- 4 MP image supports 16x9 wide frame with full 1080P HD resolution.
- Motorized varifocal lens for flexible remote zooming without loss of resolution.
- Vandal and weather resistant dome camera body for indoor and outdoor use.
- Professional-grade night vision allows users to see up to 50 feet clearly in near total darkness.
- Easily install over a single-gang electrical box.
- Powered by a single PoE cable.
- Support for 32GB MicroSD storage for basic recording and extended recording with Legrand Network Video Recorder.
- Compatible with Intuity Home Automation

Specifications

General Info

Product Line	On-Q	UPC Number	804428431428
Country Of Origin	China	Application Sector	Residential
Standard	FCC Part 15 Class B, RoHS		

Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes
---------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

IP/Analog	IP	Frame Rate	30 fps
Effective Pixels	4 MP	Zoom Ratio	2.8
Resolution	2688 x 1520 @ 30 fps / 1920 x 1080 @ 30 fps / 1280 x 720 @ 30 fps / 640 x 360 @ fps	Auto Iris Type	2.8 to 8mm, 2.8X motorized lens @ F1 (8mm)
Vertical Viewing Angle	50.25 deg		
