



On-Q
In-Wall TV Power and Cable Management Kit, Canada, White
Part No. CPT306WC1



This Legrand pre-wired kit is the perfect hassle-free solution for installers and homeowners who want to hide power and AV cables without the need for modifying electrical wiring. With this kit, extending power for a wall-mounted TV is a breeze, providing the ultimate flexibility while maintaining a clean and sleek appearance. The kit comes with an innovative decorator-based power inlet strap and a recessed box with a duplex power receptacle, providing an easy solution for concealed cabling inside the wall. This kit is ideal for those who want to enhance their home theater or office space while maintaining a professional and organized appearance.

Features & Benefits

Extend power to a wall mount TV without modifying the homes existing electrical wiring

Tamper Resistant receptacle powers multiple devices such as a TV, sound bar or streaming players

Recessed receptacle supports almost any type of power plug including right angles and wall warts

Unique decorator based power inlet strap provides flexible project support for ganging other AV connections

Hides both power and AV cables inside the wall for a clean, professional installation

Kit Includes: Recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate and the recessed box with duplex power receptacle.

Canadian Compliant - includes grounding clip

Wire Size: 14 - 2 AWG with Ground In - Wall Rated

Specifications

General Info

| | | | |
|--------------------|---------------------------------------|-----------------------|--------------------------------|
| Product Line | On-Q | Color | White |
| Finish | Glossy | Country Of Origin | China |
| Receptacle Type | 5-15R | Number of Receptacles | 2 |
| Outlet Type | Indoor, Residential, Tamper-Resistant | Package Quantity | 1 |
| Application Sector | Residential | Standard | cUL |
| Warranty Type | 1-Year | Type | Power Supply, Tamper-Resistant |

Dimensions

| | | | |
|-------------------|----------|-------------------|---------|
| Product Width US | 4.1 in | Product Weight US | 2.16 lb |
| Product Depth US | 8.75 in | Product Height US | 4.1 in |
| Product Length US | 10.25 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-------------------|------------|------------|-----|
| cUL ListingNumber | 514C & 498 | cUL Listed | Yes |
|-------------------|------------|------------|-----|

Technical Information

| | | | |
|---------------------|--------------|-----------------|------------|
| Is Tamper-Resistant | Yes | Number of Gangs | 2 |
| Temperature Rating | 32° - 122° F | Amperage | 15 A |
| Number of Poles | 3-Way | Wire Size | 14 - 2 AWG |
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |
| Connection Type | Wired | | |
