



**On-Q**  
**ENCLOSURE IN-WALL POWER KIT, 6FT - WHITE**  
Part No. CPT7526WHR6



Extend electrical power from an existing wall outlet to the Dual-Purpose Enclosure behind a wall mounted TV without ever needing to modify the home's electrical wiring. The Pre-wired 15A Tamper Resistant outlet secures into the Dual-Purpose Enclosure knockouts allowing for power and AV cables to hide inside the wall and out of sight.

## Features & Benefits

Extend electrical power from an existing wall outlet to the Legrand Dual-Purpose Enclosure behind a wall mounted TV without ever needing to modify the home's electrical wiring

Dual outlet powers multiple devices like a cable box, network switch or streaming devices

Includes everything needed to complete installation: Junction box with pre-wired outlet and 6ft in-wall rated cable, power input module, 6ft power cord, drywall saw and all necessary hardware

Pre-wired 15A Tamper Resistant outlet secures into the Dual-Purpose Enclosure knockouts allowing for power and AV cables to hide inside the wall and out of sight

Safety tested and certified power input module and 6ft in-wall rated power cable assembly

## Specifications

### General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428434863
Country Of Origin	China	Receptacle Type	5-15R
Number of Receptacles	2	Construction	Metal and Plastic
Included	Wall Plate	Wall Plate Type	Combination
Package Quantity	1	Application Sector	Residential
Warranty Type	1-Year Limited Warranty	Type	Tamper-Resistant

### Dimensions

---

Product Weight US	1.16 lb	Product Depth US	3.1 in
-------------------	---------	------------------	--------

---

Product Height US	11.0 in	Product Length US	8.0 in
-------------------	---------	-------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

ETL Listed	Yes	ETL ListingNumber	101152094CRT-001
------------	-----	-------------------	------------------

---

### Technical Information

---

Compatibility	On-Q Dual Purpose Enclosure	Wire Gauge	14 AWG
---------------	-----------------------------	------------	--------

---

Cutout	3.5 inch depth required	Amperage	15 A
--------	-------------------------	----------	------

---

Indoor/Outdoor	Indoor	Operating Temperature	32°-122°F
----------------	--------	-----------------------	-----------

---

Number of Outlets	2	Voltage	125.0 V
-------------------	---	---------	---------

---