



Pass and Seymour  
**1200 Series Cable Reel with Flying Lead 20 Amp, 12 AWG, 50 ft For Lift/Drag Applications**  
Part No. CR12L123N50F20B



Industrial-grade 1200 Series Cable Reels are precision machines, built with a minimum of components to provide years of reliable service with little or no maintenance. Made of all steel construction in the USA, these cable reels are ideal for assembly and fabrication work areas, conveyors, utility trucks, automotive and truck work bays, and much more.

## Features & Benefits

Made in USA      All steel construction with fiberglass/nylon drum, yellow powder coat finish

UL/CSA Listed

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007205831	Country Of Origin	United States
Features	Lift/Drag, Retractable	Application Sector	Commercial, Data Center, Education, Industrial
Warranty Type	1-Year	Type	Cable Reel

### Technical Information

Wire Gauge	12 AWG	Cord Length	50 ft
Amperage	20 A	Number of Conductors	3
Indoor/Outdoor	Indoor	Mobile End	Flying Lead
Operating Temperature	22°-194°F		